

CMI165

Copper Thickness Measurement with Temperature Compensation



Oxford Instruments **CMI165** provides unique temperature compensated Copper thickness measurements in an ergonomic hand-held device. Measurements on Copper are affected by the temperature of the sample. The **CMI165** accounts for temperature in the measurement of thickness ensuring accurate in-process inspection results regardless of Copper temperature. This versatile, portable gauge equipped with protective case, has a rugged and durable design that allows it to be taken into the harshest environments.



- Measure hot or cold Cu on PCBs
- Reduce waste by eliminating the need for coupons
- Measure foil or laminated Cu thickness in μm , mils or oz
- Sort Cu by weight at incoming inspection, before drilling, shearing or plating
- Quantify Cu thickness after etching or planarizing
- Verify Cu plating thickness on PCB surfaces

The Business of Science[®]



Proprietary SRP-T1 measurement probe



User Interface available in both English and Simplified Chinese

- SRP-T1 Replaceable Probe Tip – no recalibration necessary
- Spare SRP-T1 ensures no factory downtime
- Illuminated probe tip for easy positioning on copper traces

Specifications:

- Copper thickness is measured using 4-point probe electrical resistance method and conforms to standard EN 14571.
- Thickness measurement ranges
 - Copper Electroless: (0.25-12.7) μm , (0.01-0.5) mils
 - Copper Electrodeposited: (2.0-254) μm , (0.1-10) mils
- High repeatability and reliability: $\sigma \approx 0.08 \mu\text{m}$ at 20 μm (0.003 mils at 0.79 mils)
- Statistical analysis includes data recording, average, standard deviation and high-low reporting
- Measurement units in μm , mils or oz
- User interface in English or Simplified Chinese
- Measure etched traces as thin as 204 μm (8mils) without line width standards
- Store 9,690 measurements (with optional date and time stamp)

- USB 2.0 high-speed data transfer interfaced with Microsoft Excel™
- Factory calibrated and certified
- Customizable for other applications
- Static or continuous mode measurement
- Powered by regular AA batteries



Oxford Instruments Industrial Analysis

UK

Halifax Road, High Wycombe
Bucks, HP12 3SE England
Tel: +44 (0) 1494 442255
Fax: +44 (0) 1494 461033
Email: analytical@oxinst.com

China

Beijing
Tel: (8610) 6518 8160/1/2
Fax: (8610) 6518 8155
Email: info@oichina.cn

Finland

Espoo
Tel: +358 9 329 411
Fax: +358 9 3294 1300
Email: FI-Espoo_Info@oxinst.com

France

Saclay
Tel: +33 (0) 1 69 85 25 24
Fax: +33 (0) 1 69 41 86 80
Email: analytical-info@oxford-instruments.fr

Germany

Uedem
Tel: +49 (0) 2825 93 83 -0
Fax: +49 (0) 2825 93 83 -100
Email: analytical@oxford.de

Japan

Tokyo
Tel: +81 (0) 3 5245 3591
Fax: +81 (0) 3 5245 4466/4477
Email: oikkma@oxinst.co.jp

Latin America

Clearwater FL
Tel: +1 727 538 7702
Fax +1 727 538 4205
Email: oxford@gate.net

Singapore

Tel: +65 6337 6848
Fax: +65 6337 6286
Email: xrf.sales@oxford-instruments.com.sg

North America

Elk Grove Village IL
Tel: +1 847 439 4404
Fax: +1 847 439 4425
Email: sales@msys.oxinst.com

www.oxford-instruments.com

Click onto www.oxford-instruments.com for more information

Oxford Instruments, at High Wycombe, UK, operates Quality Management Systems approved to the requirements of BS EN ISO 9001. This publication is the copyright of Oxford Instruments Analytical Limited and provides outline information only which (unless agreed by the company in writing) may not be used, applied or reproduced for any purpose or form part of any order or contract or be regarded as a representation relating to the products or services concerned. Oxford Instruments' policy is one of continued improvement. The company reserves the right to alter, without notice, the specification, design or conditions of supply of any product or service. Oxford Instruments acknowledges all trade marks and registrations.

© Oxford Instruments Analytical Ltd, 2008. All rights reserved.

Part no: OIIA/046/A/0108



Certificate No FM29142

